



SKU	Designation	French Law	Length (cm)	Height (cm)	Weight (g)	Colors	MSRP
IM52DO-10133	Sauer 303 / Docter / Bas Bh4	Vente libre	4.6	0.4	150	Black	295.00 € incl. tax

### Quick and discreet mounting for Docter-type red dot sights

The **INNOMOUNT QD Slight mount** for **Sauer 303 (SN series R)** is designed for compact optics such as Docter. Its ultra-low profile and quick-release system offer clean integration and intuitive handling. In use, this combination of discretion and efficiency is much appreciated.

- **Brand** : INNOMOUNT
- **Weapon compatibility** : Sauer 303 (SN series R)
- **Lens compatibility** : Docter, Noblex, Geco, Leica Tempus, Vortex, Burris FastFire, Kahles Helia RD
- **Type** : quick assembly QD (Quick Detach)
- **Supplied with** : 2x N00032 screws
- **Materials** : High-strength aluminum / hardened steel
- **Type** : QD (Quick Detach)
- **Construction height** : 4 mm
- **Total length** : 46 mm
- **Weight** : 150 g

The **INNOMOUNT QD Slight mount** stands out thanks to its quick-release system with a retractable double lever. It opens simply via two push buttons, while remaining perfectly secure against accidental operation.

#### Reliable and intuitive QD system

The **Quick Detach** mechanism allows for virtually tool-free assembly and disassembly. Once correctly adjusted, it guarantees excellent repeatability - you disassemble, you reassemble, and everything stays in place.

#### Ultra-low profile

With a **height of only 4 mm** , this mount offers a very natural sight line. In the field, this translates into quick and instinctive target acquisition.

### **Enhanced security**

The levers are integrated into the structure to prevent any unintentional opening. This is exactly the kind of detail that is appreciated in dynamic situations.

### **Extended compatibility**

This model is compatible with many **Docter** standard red dot sights. A versatile solution for easily adapting your equipment.

## **FAQ**

### **Is this mount compatible with Docter-type optics?**

Yes, it is compatible with Docter, Noblex, Leica Tempus, Vortex, Burris FastFire and Kahles Helia RD lenses.

### **Does the QD system retain its settings after disassembly?**

Yes, once properly adjusted, the assembly guarantees excellent repeatability of the point of impact after reassembly.

### **Can the assembly open accidentally?**

No, the levers are recessed and secured by push buttons, preventing any unintentional opening.

*Les prix de vente conseillés sont mentionnés à titre indicatif. Les armuriers sont libres de vendre au prix qu'ils souhaitent. Textes et photos non contractuels, sujet à modification.*