



INNOMOUNT

NOUVEAU

SKU	Designation	French Law	Length (cm)	Height (cm)	Weight (g)	Colors	MSRP
IM52DO-10133	Sauer 303 / Docter / Bas Bh4	Vente libre	4.6	0.4	150	Black	295.00 € incl. tax

Quick and discreet mounting for Docter-type red dot sights

The **INNOMOUNT QD Slight mount** for **Sauer 303 (SN series R)** is designed for compact optics such as Docter. Its ultra-low profile and quick-release system offer clean integration and intuitive handling. In use, this combination of discretion and efficiency is much appreciated.

- **Brand** : INNOMOUNT
- **Weapon compatibility** : Sauer 303 (SN series R)
- **Lens compatibility** : Docter, Noblex, Geco, Leica Tempus, Vortex, Burris FastFire, Kahles Helia RD
- **Type** : quick assembly QD (Quick Detach)
- **Supplied with** : 2x N00032 screws
- **Materials** : High-strength aluminum / hardened steel

- **Type** : QD (Quick Detach)
- **Construction height** : 4 mm
- **Total length** : 46 mm
- **Weight** : 150 g

The **INNOMOUNT QD Slight mount** stands out thanks to its quick-release system with a retractable double lever. It opens simply via two push buttons, while remaining perfectly secure against accidental operation.

Reliable and intuitive QD system

The **Quick Detach** mechanism allows for virtually tool-free assembly and disassembly. Once correctly adjusted, it guarantees excellent repeatability - you disassemble, you reassemble, and everything stays in place.

Ultra-low profile

With a **height of only 4 mm** , this mount offers a very natural sight line. In the field, this translates into quick and instinctive target acquisition.

Enhanced security

The levers are integrated into the structure to prevent any unintentional opening. This is exactly the kind of detail that is appreciated in dynamic situations.

Extended compatibility

This model is compatible with many **Docter** standard red dot sights. A versatile solution for easily adapting your equipment.

FAQ

Is this mount compatible with Docter-type optics?

Yes, it is compatible with Docter, Noblex, Leica Tempus, Vortex, Burris FastFire and Kahles Helia RD lenses.

Does the QD system retain its settings after disassembly?

Yes, once properly adjusted, the assembly guarantees excellent repeatability of the point of impact after reassembly.

Can the assembly open accidentally?

No, the levers are recessed and secured by push buttons, preventing any unintentional opening.

Les prix de vente conseillés sont mentionnés à titre indicatif. Les armuriers sont libres de vendre au prix qu'ils souhaitent. Textes et photos non contractuels, sujet à modification.